



ApoA-IV Antibody

CATALOG NUMBER: 46-748

Specifications

SPECIES REACTIVITY:	Mouse
TESTED APPLICATIONS:	ELISA
APPLICATIONS:	ELISA: Antibody detection limit dilution 1:32,000.
IMMUNOGEN:	ApoA-IV antibody was raised against a 16 amino acid synthetic peptide near the internal region of ApoA-IV.
HOST SPECIES:	Goat

Properties

PURIFICATION:	ApoA-IV antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.
PHYSICAL STATE:	Liquid
BUFFER:	ApoA-IV antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.
CONCENTRATION:	500 ug/mL
STORAGE CONDITIONS:	Aliquot and store at -20°C. Minimize freezing and thawing.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	Apoa4, apolipoprotein A-IV, Apoa-4
ACCESSION NO.:	NP_031494.2
PROTEIN GI NO.:	110347473
OFFICIAL SYMBOL:	Apoa4
GENE ID:	11808 (mouse);

Background

FOR RESEARCH USE ONLY

December 13, 2016