



TFAP2A Antibody

CATALOG NUMBER: 46-905

Specifications

SPECIES REACTIVITY:

TESTED APPLICATIONS: ELISA

APPLICATIONS: ELISA: Antibody detection limit dilution 1:16,000.

IMMUNOGEN: TFAP2A antibody was raised against a 15 amino acid synthetic peptide near the C-Terminus of TFAP2A.

HOST SPECIES: Goat

Properties

PURIFICATION: TFAP2A antibody was purified from goat serum by ammonium sulphate precipitation followed by antigen affinity chromatography using the immunizing peptide.

PHYSICAL STATE: Liquid

BUFFER: TFAP2A antibody is supplied in Tris saline, 0.02% sodium azide, pH 7.3 with 0.5% bovine serum albumin.

CONCENTRATION: 500 ug/mL

STORAGE CONDITIONS: Aliquot and store at -20°C. Minimize freezing and thawing.

CLONALITY: Polyclonal

CONJUGATE: Unconjugated

Additional Info

ALTERNATE NAMES: tfap2a, transcription factor AP-2 alpha, cb93, fb83f04, fc31a07, wu:fb83f04, wu:fc31a07, ap2, ap2a, lockjaw, low, mob, mont blanc

ACCESSION NO.: NP_789829.1

PROTEIN GI NO.: 28849910

OFFICIAL SYMBOL: tfap2a

GENE ID: 140618

Background

REFERENCES: 1) Li W, Cornell RA. Redundant activities of Tfap2a and Tfap2c are required for neural crest induction and development of other non-neural ectoderm derivatives in zebrafish embryos. Dev Biol. 2007 Apr 1;304(1):338-54. Epub 2006 Dec 23.

FOR RESEARCH USE ONLY

December 13, 2016