



IL-4 Antibody [MP4-25D2]

CATALOG NUMBER: 77-065

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	Func, Neut
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	The MP4-25D2 monoclonal antibody specifically reacts with human Interleukin-4 (IL-4), expressed by the activated T cells and mast cells.
HOST SPECIES:	Rat

Properties

PURIFICATION:	The monoclonal antibody was purified utilizing affinity chromatography.
PHYSICAL STATE:	liquid
BUFFER:	Phosphate-buffered aqueous solution, pH7.2.
CONCENTRATION:	2.0 mg/mL
STORAGE CONDITIONS:	The product should be stored undiluted at 4°C . Do not freeze.
CLONALITY:	Monoclonal
ISOTYPE:	Rat IgG1, kappa
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	BSF1, IL-4, BCGF1, BSF-1, BCGF-1, IL4
OFFICIAL SYMBOL:	IL4
GENE ID:	3565

Background

BACKGROUND:	The MP4-25D2 monoclonal antibody specifically reacts with human Interleukin-4 (IL-4), expressed by the activated T cells and mast cells. IL-4 is species-specific and stimulates the proliferation and differentiation of B lymphocytes. It upregulates the expression of IgE receptors and class II MHC antigen. The MP4-25D2 is a neutralizing antibody and is reported to be cross-reactive with rhesus monkeys.
--------------------	---

FOR RESEARCH USE ONLY

December 13, 2016