Untitled Page Page 1 of 1



n-Heptane AR

Product No. 5177 Specifications current as of: Jun 8 2011

TEST	SPECIFICATION
Assay (CH ₃ (CH ₂) ₅ CH ₃) (by GC, corrected for water)	min. 99.0 %
Acidity (as CH ₃ COOH)	Passes Test
Residue after Evaporation	max. 0.001 %
Sulfur Compounds (as S)	max. 0.005 %
Specific Gravity at 60°/60°F	0.68 - 0.72
Thiophene	Passes Test

Product Information (not specifications):

Appearance (clear, colorless, volatile liquid)

For Laboratory, Research or Manufacturing Use