

## Medical Devices for *In Vitro* Fertilization



### Thermo Scientific Nunc 4-Well Dishes and Petri Dishes for IVF

- Mouse Embryo Assay (MEA) tested – 80% acceptance level
- 510(K) cleared for US market
- CE-marked Class IIa for IVF according to Medical Device Directive 93/42/EEC
- Produced under ISO 13485 with full lot traceability
- Certified:
  - Sterile (SAL  $10^{-6}$ )
  - Non-pyrogenic
  - USP Class VI test
  - Release test results (MEA)

Certificates of conformity on every lot

## Security, safety and reproducibility for your valuable samples

### Mouse Embryo Assay (MEA) tested

Blastocyst formation rate higher than 80% for fully expanded blastocysts both in test and control after 96 hours. The MEA test is a release test and the product will only be sold if it has passed the test.

### Certificates of Conformance

Testing results are available online for every lot. Visit <http://certificates.nunc.dk>.  
For user name and password email [certificate.nunc@thermofisher.com](mailto:certificate.nunc@thermofisher.com)

### Material

All materials have successfully passed the USP biological reactivity class VI test and ISO 10993 standards for cytotoxicity.

### Nunc IVF 4 Well Dishes

Sterile

Cat. No.	73521-354	89092-330
Description	4 Well Dish	4 Well Dish
Number of wells	4	4
Surface	NuncclonΔ	Non-treated
Airvent	-	-
Culture area, cm <sup>2</sup> /well	1.9	1.9
External dimensions, mm	66 x 66	66 x 66
Units per pack/case	4/120	4/120

### Nunc IVF Petri Dishes

Sterile

Cat. No.	89092-332	89092-334	89092-336
Description	Dish 35 x 10	Dish 60 x 15	Dish 90 x 17
Number of wells	1	1	1
Surface	Non-treated	Non-treated	Non-treated
Airvent	Yes	Yes	Yes
Culture area, cm <sup>2</sup> /well	8.8	21.5	56.7
External dimensions, mm	40 x 12	60 x 15	92 x 17



Prices, product appearance and specifications are current at the time of printing, subject to change without notice. Availability for certain products may be limited by federal, state, provincial or local licensing requirements. All prices are in U.S. dollars unless otherwise noted. Offers valid in USA and Canada, void where prohibited by law or company policy, while supplies last. Visit [vwr.com](http://vwr.com) to view our privacy policy and additional disclaimers.

VWR, forms of VWR and the VWR logo and/or design are either registered trademarks ®, trademarks ™, or service marks SM of VWR International, LLC in the United States and/or other countries. All other marks referenced herein are registered trademarks, trademarks or service marks of their respective owner(s). For a complete list of trademark owners please visit [vwr.com](http://vwr.com).

©2010 VWR International, LLC. All rights reserved.

0210

BRLSPVWRIVFDSH 0210

