


NKAP Antibody (C-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP12401b	WB, E	H	NP_078804.2 , Q8N5F7
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB31412

Application Data:

Calculated MW: 47138 Da



NKAP Antibody (C-term) (Cat. #AP12401b) western blot analysis in HepG2 cell line lysates (35ug/lane). This demonstrates the NKAP antibody detected the NKAP protein (arrow).

Gene ID:	Gene Symbol:
79576	NKAP

Other Names:

NKAP;NF-kappa-B-activating protein;

Target/Specificity:

This NKAP antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 394-415 amino acids from the C-terminal region of human NKAP.

Application Notes:

The suggested dilution is:

ELISA 1:1,000

Western blotting 1:100~500

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

NKAP Antibody (C-term) can be refrigerated at 2-8°C for up to 6 months. For long term storage,

place the at -20°C.

Precautions:

NKAP Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
