
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP2-11535

NBP2-11535

Nck Antibody (11D10)



Unit Size
0.05 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P

Species
Human, Mouse, Rat

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Purity
Ammonium sulfate precipitation

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Recombinant human protein purified from E. coli (His-Nck1).


Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin 1:200, Western Blot 1:2000

Buffer
HEPES with 0.15M NaCl, 0.01% BSA and 50% glycerol.

Images

Immunohistochemistry-Paraffin: Nck Antibody (11D10) [NBP2-11535] - Staining of human spleen. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody dilution 1:200.

Immunohistochemistry-Paraffin: Nck Antibody (11D10) [NBP2-11535] - Staining of human tonsil. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody dilution 1:200.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com