
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP2-03935

NBP2-03935

EBI3 Antibody



Unit Size
0.1 mg

Concentration
Please see the vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Primate

Host
Rabbit

Clonality
Polyclonal

Purity
Protein G purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
EBI3 is routinely seen in western blot at approximately 35 kD.


Immunogen
A portion of amino acids 120-170 of human EBI3 was used as the immunogen

Recommended Dilutions
Western Blot 2-5ug/ml

Buffer
100 ug in 200 ul PBS containing 0.05% BSA

Uses
This product is useful for Western blot analysis

Images
Western Blot: EBI3 Antibody [NBP2-03935] - analysis of EBI3 in Jurkat cell lysate in the 1) absence and 2) presence of immunizing peptide at 2 ug/ml and 3) recombinant human IL-35 protein at 5 ug/ml using EBI3 antibody.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com