Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP2-00997

NBP2-00997

CBR3 Antibody (1G6)

Unit Size
0.1 ml

Concentration
Please see the vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, IHC, IHC-P

Species
Human, Mouse, Rat, Canine, Primate

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
Full length human recombinant protein of human CBR3(NP_001227) produced in HEK293T cell.

Recommended Dilutions
Western Blot 1:500-2000, Immunohistochemistry-Paraffin 1:150, Immunohistochemistry

Buffer
PBS (PH 7.3) containing 1% BSA, 50% glycerol

Images (more available at www.novusbio.com/NBP2-00997)

Western Blot: CBR3 Antibody (1G6) [NBP2-00997] Analysis of extracts (35ug) from 9 different cell lines by using anti-CBR3 monoclonal antibody.



Immunohistochemistry-Paraffin: CBR3 Antibody (1G6) [NBP2-00997] - Staining of paraffin-embedded Human prostate tissue using anti-CBR3 mouse monoclonal antibody.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com