
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP2-01819

NBP2-01819

Calpastatin Antibody (1E7)



Unit Size
0.1 ml

Concentration
Please see the vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, FLOW, IHC, IHC-P

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Affinity purified

Preservative
0.02% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
Full length human recombinant protein of human CAST(NP_001741) produced in HEK293T cell.


Recommended Dilutions
Western Blot 1:2000, Immunohistochemistry-Paraffin 1:150, Flow Cytometry 1:100, Immunohistochemistry

Buffer
PBS (PH 7.3) containing 1% BSA, 50% glycerol

Images (more available at www.novusbio.com/NBP2-01819)



Western Blot: Calpastatin Antibody (1E7) [NBP2-01819] - HEK293T cells were transfected with the pCMV6-ENTRY control (Left lane) or pCMV6-ENTRY Calpastatin (Right lane) cdna for 48 hrs and lysed. Equivalent amounts of cell lysates (5 ug per l... See more at www.novusbio.com/NBP2-01819



Immunohistochemistry-Paraffin: Calpastatin Antibody (1E7) [NBP2-01819] Staining of paraffin-embedded Human prostate tissue using anti-Calpastatin mouse monoclonal antibody.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com