
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-97745

NBP1-97745

TSC22D1 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 125 and 175 of human TSC22 (TGFB-stimulated clone 22) domain family, member 1 using the numbering given in entry NP_904358.2 (GeneID 8848).

Recommended Dilutions
Immunoprecipitation 2 - 10 mcg/mg lysate, Western Blot 1:2000 - 1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-97745

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com