
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-97128

NBP1-97128

Turkey IgG, H/L Chains Protein [Texas Red]



Unit Size
1 mg

Concentration
Lyoph

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Species
Turkey

Isotype
IgG

Conjugate
Texas Red

Preservative
0.01% Sodium Azide

Updated 3/9/2013 2.0

Buffer
Potassium Phosphate, 0.15 M Sodium Chloride pH 7.2 Restore with 1.0 mL of deionized water (or equivalent).Restore with 1.0 mL of deionized water (or equivalent).

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-97128

Notes
Stabilizer: 10 mg/ml Bovine Serum Albumin (BSA)-Immunoglobulin and Protease free
Color: Red ,Excitation Wavelength: 596 ,Emission Wavelength: 620

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com