
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-80567

NBP1-80567

MEF2D Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The epitope reconized by this antibody maps to a region between residue 475 and 521 of human Myocyte Enhancer Factor 2D using the numbering given in entry NP_005911.1 (GeneID 4209).

Recommended Dilutions
Immunoprecipitation 2 - 10 ug/mg, Western Blot 1:2000 - 1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
This antibody works in Western Blot, Immunoprecipitation.

Images
Western Blot: MEF2D Antibody [NBP1-80567] - Whole cell lysate from HeLa (15 and 50 mcg for WB; 1 mg for IP, 20% of IP loaded), 293T (T; 50 mcg), Jurkat (J; 50 mcg) and mouse NIH3T3 (M; 50 mcg) cells. Antibodies: Affinity purified rabbit anti... See more at www.novusbio.com/NBP1-80567



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com