
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-77260

NBP1-77260

TRPC6 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Peptide affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Antibody was raised against a 14 amino acid peptide from near the carboxy terminus of human TRPC6 (AAH93658).

Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin 10 ug/ml, Western Blot 0.5-1 ug/ml

Buffer
PBS

Images

Western Blot: TRPC6 Antibody [NBP1-77260] - Mouse lung tissue lysate with TRPC6 antibody at (A) 0.5, (B) 1 and (C) 2 ug/ml.

Immunohistochemistry-Paraffin: TRPC6 Antibody [NBP1-77260] - Mouse lung tissue with TRPC6 antibody at 10 ug/ml.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com