
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-77309

NBP1-77309

BACE2 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Antibody was raised against a synthetic peptide corresponding to amino acids 44 to 59 of human BACE2.

Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

Buffer
PBS containing 0.02% sodium azide.

Uses
BACE2 can be used for detection of BACE2 by Western blot at 0.5 to 1 mg/ml.

Images
Western Blot: BACE2 Antibody [NBP1-77309] - Human (A) and mouse (B) heart tissue lysates with BACE2 antibody at 1 ug/ml.

Immunohistochemistry-Paraffin: BACE2 Antibody [NBP1-77309] - Mouse heart with BACE2 antibody at 10 ug/ml.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com