
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-77360

NBP1-77360

THEM4 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Antibody was raised against an 18 amino acid peptide near the center of human THEM4

Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

Buffer
PBS containing 0.02% sodium azide.

Uses
ELISA, Western Blot, Immunohistochemistry-Paraffin

Images

Western Blot: THEM4 Antibody [NBP1-77360] - Human liver tissue lysate with THEM4 antibody at (A) 1 and (B) 2 ug/ml.

Immunohistochemistry-Paraffin: THEM4 Antibody [NBP1-77360] - Human liver tissue with THEM4 antibody at 2.5 ug/ml.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com