
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-76442

NBP1-76442

Ube2V1 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Ion exchange chromatography

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Antibody was raised against a peptide corresponding to 15 amino acids near the C-terminus of human UEV1A.

Recommended Dilutions
ELISA, Western Blot

Buffer
PBS containing 0.02% sodium azide.

Uses
UEV1A antibody can be used for detection of UEV1A by Western blot at 1 to 2 mg/ml. Anti-UEV1A may also recognize other isoforms of UEV1A.

Images
Western Blot: Ube2V1 Antibody [NBP1-76442] - Jurkat cell lysates with Ube2V1 antibody at (A) 1, (B) 2, and (C) 4 ug/ml.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com