
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-76619

NBP1-76619

TSC2 Antibody



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, ICC/IF, IHC, IHC-P

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
TSC2 (NT) was raised against a 14 amino acid peptide from near the amino terminus of human TSC2.


Recommended Dilutions
ELISA, Immunocytochemistry/Immunofluorescence 10 ug/ml, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot 4ug/ml

Buffer
PBS containing 0.02% sodium azide.

Uses
TSC2 antibody can be used for the detection of TSC2 by Western blot at 1 mg/ml.

Images

Western Blot: TSC2 Antibody [NBP1-76619] - L1210 cell lysate with TSC2 antibody at (A) 2 and (B) 4 ug/ml.



Immunocytochemistry/Immunofluorescence: TSC2 Antibody [NBP1-76619] - L1210 cells with TSC2 antibody at 10 ug/ml.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com