
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-71774C

NBP1-71774C

TRPV1 Antibody [DyLight 650]



Unit Size
0.1 ml

Concentration
1.03 mg/ml

Storage
Store at 4C in the dark.

Applications
ICC/IF, IHC, IHC-P

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 650

Purity
Affinity purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
A genomic peptide made to an C-terminal region of the human TRPV1 protein (within residues 725-839). [Swiss-Prot Q8NER1]

Recommended Dilutions
Immunohistochemistry-Paraffin 1:200, Immunocytochemistry/Immunofluorescence 1:50-1:100, Immunohistochemistry

Buffer
PBS, 30% glycerol

Uses
This TRPV1 antibody is useful for ICC/IF and IHC-paraffin embedded tissues. Prior to immunostaining paraffin tissues, antigen retrieval with sodium citrate buffer (pH 6.0) is recommended.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-71774C

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com