
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-71813

NBP1-71813

SUV3L1 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen for this product maps to a region between residue 736 and 786 of human Suppressor of Var1, 3-like 1 using the numbering given in entry NP_003162.2 (GeneID 6832).

Recommended Dilutions
Immunoprecipitation 2 - 5 mcg/mg, Western Blot 1:2000 - 1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
This antibody works in Western Blot, Immunoprecipitation.

Images
Western Blot: SUV3L1 Antibody [NBP1-71813] - Whole cell lysate from HeLa (5, 15 and 50 mcg for WB; 1 mg for IP, 20% of IP loaded) and 293T (T; 50 mcg) cells. Affinity purified rabbit anti-SUV3 antibody used for WB at 0.04 mcg/ml (A) and 1 mc... See more at www.novusbio.com/NBP1-71813



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com