Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-59555

# NBP1-59555

# SLC25A6 Antibody

## Unit Size
0.05 mg

## Concentration
lyoph

## Storage
Store at -20C. Avoid freeze-thaw cycles.

## Applications
WB

## Species
Human

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Peptide affinity purified

## Preservative
No Preservative

Updated 3/9/2013 2.0


## Immunogen
Synthetic peptides corresponding to SLC25A6(solute carrier family 25 (mitochondrial carrier; adenine nucleotide translocator), member 6) The peptide sequence was selected from the N terminal of SLC25A6. Peptide sequence LQVQHASKQIAADKQYKGI

## Recommended Dilutions
Western Blot

## Buffer
PBS & 2% Sucrose lyophilized with the antibody.Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 50ul of distilled water. Vortex followed by centrifuge again to pellet the solution.Final concentration is 1 mg/ml in PBS buffer

## Uses
This is a rabbit polyclonal antibody against SLC25A6 and was validated on Western blot.

## Images
Western Blot: SLC25A6 Antibody [NBP1-59555] - Titration: 0.2-1 ug/ml, Positive Control: Human heart.




*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com