
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-59696

NBP1-59696

EDG8 Antibody



Unit Size
0.1 mg

Concentration
lyoph

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, IHC, IHC-P

Species
Human, Mouse, Rat, Canine, Drosophila, Zebrafish

Host
Rabbit

Clonality
Polyclonal

Purity
IgG purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
Synthetic peptides corresponding to EDG8(endothelial differentiation, sphingolipid G-protein-coupled receptor, 8) The peptide sequence was selected from the N terminal of EDG8. Peptide sequence MESGLLRPAPVSEVIVLHYNYTGKLRGARYQPGAGLRADAVVCLA

Recommended Dilutions
Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot 2.5ug/ml

Buffer
PBS & 2% Sucrose lyophilized with the antibody.Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 100ul of distilled water. Vortex followed by centrifuge again to pellet the solution.Final concentration is 1 mg/ml in PBS buffer

Uses
This is a rabbit polyclonal antibody against EDG8 and was validated on Western Blot and immunohistochemistry-paraffin

Images
Western Blot: EDG8 Antibody [NBP1-59696] - Jurkat cell lysate, Antibody Titration: 2.5ug/ml

Immunohistochemistry-Paraffin: EDG8 Antibody [NBP1-59696] - Human Intestine Tissue, antibody concentration 4-8ug/ml. Cells with positive label: Epithelial cells of intestinal villus (indicated with arrows) 400X magnification.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com