NBP1-50802

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-50802

# NBP1-50802

# uPA Receptor Antibody

## Unit Size
0.1 mg

## Concentration
0.5 mg/ml

## Storage
Store at -20C. Avoid freeze-thaw cycles.

## Applications
WB

## Species
Rat

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Affinity purified

## Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


## Immunogen
Synthetic peptide surrounding amino acid 51 of rat uPAR

## Recommended Dilutions
Western Blot

## Buffer
(PBS), pH 7.2, containing 30% glycerol, 0.5% BSA and 0.01% Thimerosal.

## Uses
Western Blot (0.5-1 ug/ml). The antibody recognizes 33 kDa rat uPAR.

## Images
Western Blot: uPA Receptor Antibody [NBP1-50802]




*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com