
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-49540

NBP1-49540

SIRT1 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
A genomic peptide made to an internal region of the human SIRT1 protein (within residues 400-550). [Swiss-Prot Q96EB6]

Recommended Dilutions
Immunocytochemistry/Immunofluorescence, Immunohistochemistry 1:150, Western Blot 1:1000


Buffer
PBS, 0.1% BSA, 50% glycerol

Uses
This SIRT1 antibody is useful in IHC and Western blot. In Western blot a band is seen ~105 kDa.

Images
Western Blot: SIRT1 Antibody [NBP1-49540] - Analysis of SIRT1 in HeLa whole cell lyates.



Immunohistochemistry: SIRT1 Antibody [NBP1-49540] - Immunohistochemical analysis of SIRT1 in human renal cell carcinoma.



Notes
Manufactured by Genomic Antibody Technology™. GAT FAQs

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com