
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-45282R

NBP1-45282R

SNX27 Antibody [DyLight 550]



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF

Species
Human, Mouse, Rat, Bovine

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 550

Purity
Affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
Synthetic peptide made to an internal portion of the human protein (within residues 150-200). [Swiss-Prot# Q96L92]

Recommended Dilutions
Immunocytochemistry 1:50 - 1:200
Immunofluorescence 1:50 - 1:200
Western Blot 0.5 ug/ml

Buffer
50mM sodium borate

Uses
This SNX27 antibody is useful for Western blot, where a band is seen ~64 kDa. This SNX27 antibody is also useful for immunocytochemistry/immunofluorescence.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-45282R

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com