
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-45283

NBP1-45283

SNX27 Antibody



Unit Size
0.1 ml

Concentration
1 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-P

Species
Human, Mouse, Rat, Bovine, Zebrafish

Molecular Weight
65kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Synthetic peptide made to an internal portion of human SNX27 (within residues 450-500). [Swiss-Prot# Q96L92]


Recommended Dilutions
Immunocytochemistry/Immunofluorescence 1:50 - 1:200, Immunohistochemistry, Immunohistochemistry-Paraffin 1:100, Western Blot 1.0 ug/ml

Buffer
PBS, 30% glycerol


Uses
This SNX27 antibody is useful for Immunocytochemistry/Immunofluorescence, Immunohistochemistry on paraffin embedded sections and Western blot, where a band is seen at ~65 kDa. Prior to immunostaining paraffin tissues, antigen retrieval with sodium citrate buffer (pH 6.0) is recommended.

Images (more available at www.novusbio.com/NBP1-45283)

Western Blot: SNX27 Antibody [NBP1-45283] - Analysis of SNX27 on mouse brain extracts.



Immunocytochemistry/Immunofluorescence: SNX27 Antibody [NBP1-45283] - Detection of SNX27 (Green) in Hela cells using NBP1-45283. Nuclei (Blue) are counterstained using Hoechst 33258.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com