
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-45694

NBP1-45694

Matrilin 2 Antibody



Unit Size
0.1 mg

Concentration
Please see the vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


Immunogen
Synthetic peptide corresponding to residues surrounding amino acids 931 of human Matrilin-2.

Recommended Dilutions
Western Blot

Buffer
phosphate-buffered saline (PBS) containing 30% glycerol, 0.5% BSA

Uses
Western blotting (0.5-4ug/ml). However, the optimal concentrations should be determined individually. The antibody recognizes 120-150 kDa Matrilin-2 from samples of human, mouse and rat origins. An additional ~55 kDa band and a ~38 kDa band can also be detected in rat kidney and Jurkat cells, individually. Other species have not been determined.

Images
Western Blot: Matrilin 2 Antibody [NBP1-45694]



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com