
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-44150

NBP1-44150

AVPR1A Antibody



Unit Size
0.05 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -80C long term. Avoid freeze-thaw cycles.

Applications
IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Peptide affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
This product is specific for AVPR1A. Unless other species reactivities are specified there is no testing data currently available.


Immunogen
3rd cytoplasmic domain of human

Recommended Dilutions
Immunohistochemistry, Immunohistochemistry-Paraffin

Buffer
Phosphate buffered saline, PH 7.7

Uses
This product is useful for Immunohistochemistry-Paraffin

Images
Immunohistochemistry-Paraffin: AVPR1A Antibody [NBP1-44150] - Staining of human kidney. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com