
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-44369

NBP1-44369

TM9SF4 Antibody



Unit Size
0.05 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -80C long term. Avoid freeze-thaw cycles.

Applications
IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
This product is specific for Transmembrane 9 Superfamily Member 4 (TM9SF4/KIAA0255). Unless other species reactivities are specified there is no testing data currently available.

Immunogen
Synthetic peptide - KLH conjugated, N-terminal domain of human TM9SF4

Recommended Dilutions
Immunohistochemistry-Paraffin 10 ug/ml, Immunohistochemistry


Buffer
PBS, pH 7.7

Images

Immunohistochemistry-Paraffin: TM9SF4 Antibody [NBP1-44369] - Human Placenta (formalin-fixed, paraffin-embedded) stained with TM9SF4 antibody LS-A9853 followed by biotinylated goat anti-rabbit IgG secondary antibody, alkaline phosphatase-str... See more at www.novusbio.com/NBP1-44369



Immunohistochemistry-Paraffin: TM9SF4 Antibody [NBP1-44369] - Human Pancreas (formalin-fixed, paraffin-embedded) stained with TM9SF4 antibody LS-A9853 followed by biotinylated goat anti-rabbit IgG secondary antibody, alkaline phosphatase-str... See more at www.novusbio.com/NBP1-44369



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com