Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-44487

NBP1-44487

UBE2T Protein

Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at -80C. Avoid freeze-thaw cycles.

Applications
ELISA, PAGE

Species
Human

Purity
Protein

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This is a UBE2T Protein (1-197aa). Human recombinant protein expressed in E.coli. His tag increases size to 205aa


Immunogen
MQRASRLKRE LHMLATEPPP GITCWQDKDQ MDDLRAQILG GANTPYEKGV FKLEVIIPER YPFEPPQIRF LTPIYHPNID SAGRICLDVL KLPPKGAWRP SLNIATVLTS IQLLMSEPNP DDPLMADISS EFKYNKPAFL KNARQWTEKH ARQKQKADEE EMLDNLPEAG DSRVHNSTQK RKASQLVGIE KKFHPDVLEH HHHHH

Recommended Dilutions
ELISA
SDS-Page

Buffer
20mM Tris-HCl buffer(pH 8.0) containing 10% glycerol 1mM DTT.

Uses
This product is useful for ELISA and SDS-Page. The purity of this protein is > 95% by SDS - PAGE. This recombinant protein was expressed in E.Coli bacteria. The endotoxin levels of this protein have not yet been determined.

Images
SDS-Page: UBE2T Protein [NBP1-44487] - UBE2T, 23.6 kDa (205aa), confirmed by MALDI-TOF with a purity of 95% by SDS - PAGE



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com