
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-33484

NBP1-33484

Maxi Potassium channel beta Antibody



Unit Size
0.1 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0

Immunogen
Recombinant fragment corresponding to a region within amino acids 1 and 191 of KCNMB1 (Uniprot ID#Q16558)


Recommended Dilutions
Western Blot 1:500-1:3000

Buffer
0.1M Tris, 0.1M Glycine, 20% Glycerol (pH7).


Uses
Western blot. The usefulness of this product in other applications has not been determined.

Images

Western Blot: Maxi Potassium channel beta Antibody [NBP1-33484] - Sample (30 ug of whole cell lysate) A: A431 B: H1299 12% SDS PAGE; antibody diluted at 1:1000.



Western Blot: Maxi Potassium channel beta Antibody [NBP1-33484] - Sample (50 ug of whole cell lysate) A: mouse heart 12% SDS PAGE; antibody diluted at 1:10000.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com