
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-32252

NBP1-32252

SLC20A1 Antibody



Unit Size
0.1 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse

Molecular Weight
74kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


Immunogen
Recombinant fragment corresponding to a region within amino acids 262 and 547 of SLC20A1 (Uniprot ID#Q8WUM9)

Recommended Dilutions
Western Blot 1:500-1:3000


Buffer
0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Images

Western Blot: SLC20A1 Antibody [NBP1-32252] - Sample (30 ug of whole cell lysate) A: H1299 7. 5% SDS PAGE SLC20A1 antibody diluted at 1:1000.



Western Blot: SLC20A1 Antibody [NBP1-32252] - Sample (50 ug of whole cell lysate) A: Mouse brain 7. 5% SDS PAGE; antibody diluted at 1:1000.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com