
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-32461

NBP1-32461

TAF15 Antibody



Unit Size
0.1 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-P

Species
Human, Mouse, Xenopus (Negative)

Molecular Weight
62kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0

Immunogen
Recombinant fragment corresponding to a region within amino acids 15 and 279 of TAFII68 (Uniprot ID#Q92804)


Recommended Dilutions
Immunocytochemistry/Immunofluorescence 1:100 - 1:200, Immunohistochemistry, Immunohistochemistry-Paraffin 1:100 - 1:500, Western Blot 1:500 - 1:3000

Buffer
0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Uses
Western blot. The usefulness of this product in other applications has not been determined.

Images (more available at www.novusbio.com/NBP1-32461)

Western Blot: TAF15 Antibody [NBP1-32461] - (30 ug whole cell lysate) A:Raji 7.5% SDS PAGE diluted at 1:1000



Immunocytochemistry/Immunofluorescence: TAF15 Antibody [NBP1-32461] - Paraformaldehyde-fixed HeLa, using antibody at 1:200 dilution.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com