
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-31374

## NBP1-31374

# NULP1 Antibody



## Unit Size
0.1 mg

## Concentration
Concentrations vary lot to lot. See vial label for concentration.

## Storage
Store at -20C. Avoid freeze-thaw cycles.

## Applications
WB, ICC/IF, IHC, IHC-P

## Species
Human

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Affinity purified

## Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0

## Immunogen
Recombinant fragment corresponding to a region within amino acids 427 and 676 of NULP1 (Uniprot ID#Q9BQ70)


## Recommended Dilutions
Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

## Buffer
0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7).


## Uses
Immunofluorescence, Immunohistochemistry-Paraffin, Western blot. The usefulness of this product in other applications has not been determined.

## Images (more available at www.novusbio.com/NBP1-31374)

Western Blot: NULP1 Antibody [NBP1-31374] - Sample (30 ug of whole cell lysate) A: Hela 7. 5% SDS PAGE, antibody diluted at 1:500.




Immunocytochemistry/Immunofluorescence: NULP1 Antibody [NBP1-31374] - Paraformaldehyde-fixed HeLa, using antibody at 1:200 dilution.



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com