
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-26596

NBP1-26596

SMG9 Antibody



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
IP, WB (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 470 and 520 of human suppressor with morphogenetic effect on genitalia protein 9 using the numbering given in entry NP_061981.2 (GeneID 56006).

Recommended Dilutions
Immunoprecipitation 5 -10 ug/mg lysate, Western Blot (Negative)

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Images
Immunoprecipitation: SMG9 Antibody [NBP1-26596] - Whole cell lysate from HeLa cells. Antibodies: Affinity purified rabbit used for IP at 10 mcg/mg lysate. SMG9 was also immunoprecipitated by rabbit anti-SMG9 antibody NBP1-26595, which recog... See more at www.novusbio.com/NBP1-26596



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com