Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-26612

NBP1-26612

MID1 Antibody

Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 617 and 667 of human midline 1 using the numbering given in entry NP_000372.1 (GeneID 4281).

Recommended Dilutions
Immunoprecipitation (Negative), Western Blot 1:2000 -1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for western blot. It is not recommended for immunoprecipitation.

Images
Western Blot: MID1 Antibody [NBP1-26612] - Whole cell lysate from HeLa (5, 15 and 50 ug) and 293T (T; 50 ug) cells. Antibody used at 1 ug/ml.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com