
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-28666

NBP1-28666

OLIG1 Antibody



Unit Size
0.1 ml

Concentration
Please see the vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IP

Species
Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Protein A purified

Preservative
No Preservative

Updated 3/9/2013 2.0


Immunogen
Recombinant mouse Olig1

Recommended Dilutions
Immunocytochemistry/Immunofluorescence 1:1000
Immunohistochemistry 1:1000
Immunoprecipitation 1:50
Western Blot 1:3000

Buffer
100 mM Glycine, 200 mM Tris, pH 8.0.

Uses
Detects ~27 kDa Olig1 protein in Western blots.

Images
Western Blot: OLIG1 Antibody [NBP1-28666] - Neonatal rat brain lysate showing specific immunolabeling of the ~ 27k Olig1 protein.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com