
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-05936H

NBP1-05936H

AGR2 Antibody [HRP]



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
IHC, IHC-P

Species
Human, Mouse, Bovine

Host
Rabbit

Clonality
Polyclonal

Conjugate
HRP

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Anterior Gradient 2

Immunogen
Synthetic peptide made to an N-terminal portion of the mouse protein (within residues 1-50). [Swiss-Prot# O88312]

Recommended Dilutions
Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer
PBS

Uses
This antibody is useful for immunohistochemistry paraffin sections.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-05936H

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com