Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-05958

NBP1-05958

SOS2 Antibody

Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 1282 and 1332 of human son of sevenless ortholog 2 using the numbering given in entry NP_008870.2 (GeneID 6655).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Images
Western Blot: SOS2 Antibody [NBP1-05958] - Samples: Whole cell lysate from HeLa and 293T cells.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com