
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-19028

NBP1-19028

TIPIN Antibody



Unit Size
0.2 ml

Concentration
Lyoph

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, IHC, IHC-Fr, IHC-P

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Reacts specifically with human 34 kDa protein

Immunogen
Synthetic peptide derived from Nter domain of human TIPIN

Recommended Dilutions
Western Blot 1:200 to 1:2000, Immunohistochemistry-Frozen 1:50 to 1:500, Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer
Lyophilized Whole Rabbit antisera. Reconstitute in 200 ul of distilled water.

Uses
This antibody is useful for Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin, Western Blot

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-19028

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com