
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-00085R

NBP1-00085R

Beclin 1 Antibody (4H10) [DyLight 550]



Unit Size
0.1 ml

Concentration
1.2 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, IHC, IHC-P

Species
Human, Mouse, Rat, Bovine, Chicken, Equine, Primate, Porcine

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Conjugate
DyLight 550

Purity
IgG purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Beclin 1 (4H10)

Immunogen
Full length human Beclin 1 protein [Swiss-Prot# Q14457]

Recommended Dilutions
Western Blot 2.0 ug/ml, Immunohistochemistry-Paraffin 1:50- 1:100, Immunohistochemistry

Buffer
50mM sodium borate

Uses
This antibody is useful for Western blot, where a band is seen ~52 kDa. This antibody is also useful for immunohistochemistry-Paraffin.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-00085R

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com