
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-02826

NBP1-02826

MRP8 Antibody (CF-145)



Unit Size
0.05 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, FLOW, ICC/IF, IHC, IHC-P

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG2b

Purity
Protein G purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Purified human Calgranulin A


Immunogen
Purified human Calgranulin A

Recommended Dilutions
Flow Cytometry, Immunocytochemistry/Immunofluorescence, Immunohistochemistry 2.5 ug/mL, Immunohistochemistry-Paraffin 2.5 ug/mL, Western Blot

Buffer
PBS

Uses
For IHC: Use heat induced antigen retrieval in pH 6.0 citrate buffer.

Images
Immunohistochemistry-Paraffin: MRP8 Antibody (CF-145) [NBP1-02826] - Staining of human spleen, neutrophils. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 5 ug/ml... See more at www.novusbio.com/NBP1-02826



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com