
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-04268

NBP1-04268

Calmodulin Antibody (J4D8)



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA

Species
Human, Mouse

Molecular Weight
17kDa

Host
Mouse

Clonality
Monoclonal

Isotype
IgG2a Kappa

Purity
Protein G purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Recombinant human Calmodulin (1-149aa) purified from E. coli (NP_001734).

Recommended Dilutions
ELISA, Western Blot 1:500-1000

Buffer
PBS (pH 7.4)

Images
Western Blot: Calmodulin Antibody (J4D8) [NBP1-04268] - Cell lysates of NIH3T3 (50ug) were resolved by SDS-PAGE, transferred to NC membrane and probed with anti-human Calmodulin (1:500). Proteins were visualized using a goat anti-mouse secon... See more at www.novusbio.com/NBP1-04268



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com