
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBC1-18481

NBC1-18481

TNFSF13B Protein



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at -80C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human

Purity
Protein

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This protein is from amino acids 134-285


Immunogen
MRGSHHHHHHGMASMTGGQQMGRDLYDDDDKDRWGSHMAVQGPEETVTQDCLQLIAD SETPTIQKGSYTFVPWLLSFKRGSALEEKENKILVKETGYFFIYGQVLYTDKTYAMGHLIQRK KVHVFGDELSLVTLFRCIQNMPETLPNNSCYSAGIAKLEEGDELQLAIPRENAQISLDGDVTF FGALKLL

Recommended Dilutions
Western Blot

Buffer
Liquid in 20mM Tris pH 8.0, 5mM DTT

Uses
Useful in Western Blot

Images
SDS-Page: TNFSF13B Protein [NBC1-18481] - BLyS, 21 kDa (190 aa) with a purity of 95% by SDS - PAGE



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com