
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-1486

NB600-1486

MMP15 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
IHC, IHC-P

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
MMP15

Immunogen
A synthetic peptide from the catalytic domain of mouse MMP15 protein.

Recommended Dilutions
Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer
PBS, 1% BSA, pH 7.6

Uses
IHC-P: 10 min at RT. No special pretreatment is required for the immunohistochemical staining of formalin/paraffin tissues.

References
Sena P, Mariani F, Marzona L et al. Matrix metalloproteinases 15 and 19 are stromal regulators of colorectal cancer development from the early stages Int J Oncol 2012 Jul [PMID: 22576687] (IHC, ICC/IF, WB, Human

Images
Human placenta stained with Anti-MMP-15 antibody, Cat# NB600-1486



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com