
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-235C

NB600-235C

Blimp-1 Antibody (3H2-E8) [DyLight 650]



Unit Size
0.1 ml

Concentration
1.2 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ELISA, FLOW, ICC/IF, IHC, IHC-P

Species
Human, Mouse, Porcine

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Conjugate
DyLight 650

Purity
Protein G purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This is specific for the Blimp-1.

Immunogen
A fragment of the mouse Blimp-1 (residues 199-409).


Recommended Dilutions
ELISA, Flow Cytometry 8 ug/mL, Immunocytochemistry/Immunofluorescence 1:50 - 1:200, Immunohistochemistry, Immunohistochemistry-Paraffin 1:200, Western Blot 1:1000

Buffer
50mM sodium borate


Uses
This antibody is useful for ELISA, Flow Cytometry, Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin and Western Blot applications

Images (more available at www.novusbio.com/NB600-235C)

Flow Cytometry: Blimp-1 Antibody (3H2-E8) [DyLight 650] [NB600-235C] - Blimp-1 expression by IL-10+ (black line), IL-10- (dotted line) or CD8+ (thin, shaded line) cells (Tedder Lab; Duke Univ)



Flow Cytometry: Blimp-1 Antibody (3H2-E8) [DyLight 650] [NB600-235C] - IL-10+Blimp-1-, IL-10+Blimp-1+, IL-10-Blimp-1+ and IL-10-Blimp-1- cells, % total living single splenic CD19+ cells of 3 total mice (Tedder Lab; Duke Univ)



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com