
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-424

NB600-424

MSH2 Antibody [Agarose Immobilized]



Unit Size
0.1 mg

Concentration
Please see the vial label for concentration.

Storage
Store at 4C. Do not freeze.

Applications
IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Conjugate
Agarose Immobilized

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Rabbit anti-human MSH2 affinity purified Antibodies were coupled to agarose beads using a cyanogen bromide method.

Recommended Dilutions
Immunoprecipitation

Buffer
Phosphate Buffered Saline (PBS)

Uses
This antibody is useful for Immunoprecipitation 15 -25 mcl of gel slurry per 1 -1 mg of protein lysate or extract.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-424

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com