
NB600-455

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-455

NB600-455

AU1 Epitope Tag Antibody



Unit Size
1.0 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, ELISA, ICC/IF, IP

Species
Non-species specific

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
Rabbits were immunized with AU1 (DTYRYI) conjugated to KLH. Antibody was isolated by affinity chromatography using the peptide immobilized on solid support.

Recommended Dilutions
ELISA, Immunocytochemistry/Immunofluorescence 1:100- 1:400, Immunoprecipitation 1 - 4 ug/mg lysate, Western Blot 1:1000-1:10000

Buffer
Phosphate Buffered Saline (PBS)

Uses
This antibody is useful for ELISA, Western Blot and Immunocytochemistry

Images
Western Blot: AU1 Epitope Tag Antibody [NB600-455] - 200, 100, or 50 ng of E. coli whole cell lysate expressing a multi-tag fusion protein. Antibody used at 0.04 ug/ml (1:25,000).



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com