
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-503G

NB600-503G

Beta Actin Antibody [DyLight 488]



Unit Size
0.05 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF, IP

Species
Human, Mouse, Rat, Primate

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 488

Purity
Immunogen affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Beta actin

Immunogen
Synthetic peptide derived from the N-terminus of Human Beta-Actin.

Recommended Dilutions
immunofluorescence , immunoprecipitation , Western Blot 1:1000-1:5000

Buffer
50mM sodium borate

Uses
Western blotting, Immunoprecipitation, Immunofluorescence

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-503G

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com