
NB200-579

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB200-579

NB200-579

E. Coli Antibody



Unit Size
0.5 ml

Concentration
4.5 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
ELISA, ICC/IF

Species
Non-species specific

Host
Rabbit

Clonality
Polyclonal

Purity
Protein A purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Reacts with all "O" and "K" antigenic serotypes of Escherichia coli.

Immunogen
Mixtures of E.coli serotypes.

Recommended Dilutions
ELISA, Immunocytochemistry/Immunofluorescence

Buffer
0.01M PBS. pH 7.2

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB200-579

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com